

multicolor

translucency gradient

High Translucent

49 % translucency
flexural strength > 650 MPa
bridges with up to 3 units



Variants
multicolor
4 light variations
3 dark variations
1 bleach shade

Extra Translucent

45 % translucency
flexural strength > 1,150 MPa
suitable for a wide range
of indications



Variants
multicolor
4 light variations
3 dark variations
1 bleach shade

Multi Translucent

> 49 % bis ~40 % translucency
flexural strength > 800 MPa to 1,150 MPa
suitable for a wide range
of indications




Variants
gradual transition
16 VITA® shades and 3
bleaching colours

monochromatic

Extra Translucent

45 % translucency
flexural strength > 1,150 MPa
suitable for a wide range of
indications



Variants
monochromatic
white

Translucent

40 % translucency
flexural strength > 1,150 MPa
suitable for a wide range of
indications




Variants
monochromatic
VITA® shades
A1-A4, B2, C2, D2

Variants
white

Opaque

35 % translucency
flexural strength > 1,150 MPa
suitable for a wide range of
indications



Variants
monochromatic
VITA® shades
A1-A4, B2, C2, D2


Variants
white

Why does pritidenta offer so many different translucencies, shades and heights?

Each lab or milling center has its own specific requirements regarding result, price, translucency and area of application: priti®multidisc ZrO₂ offers the right solution for every need - Good to know you have a choice when you need it!

VITA® color designations are registered trademarks of VITA Zahnfabrik H. Rauter GmbH & Co. KG, Bad Säckingen, Germany

Enthusiasm
is our passion



Discover the pritidenta portfolio at:
www.pritidenta.com/en/products/



pritidenta® GmbH
Meisenweg 37
D-70771 Leinfelden-Echterdingen
Germany


Phone +49 (0) 711 32 06 56 0
Fax +49 (0) 711 32 06 56 99
info@pritidenta.com
www.pritidenta.com












Product-Overview

priti®multidisc ZrO₂

- ◆ Translucency
- ◆ Added value & Aesthetics
- ◆ Shades Classification



	Multi Translucent			
balanced shade and translucency gradient	 <p>priti®multidisc ZrO₂ Multi Translucent 16 VITA® shades A1-D4 and 3 bleaching shades</p>			
	Opaque	Translucent	Extra Translucent	High Translucent
Multicolor (Gradient + Multipositioning)			 <p>priti®multidisc ZrO₂ Shades Alight - Dlight + Bleach multicolor Extra Translucent</p>	 <p>priti®multidisc ZrO₂ Shades Alight - Dlight + Bleach multicolor High Translucent</p>
Monochromatisch	 <p>priti®multidisc ZrO₂ VITA® shades A1-A4, B2, C2, D2 Opaque</p>	 <p>priti®multidisc ZrO₂ VITA® shades A1-A4, B2, C2, D2 Translucent</p>		
white	 <p>priti®multidisc ZrO₂ white Opaque</p>	 <p>priti®multidisc ZrO₂ white Translucent</p>	 <p>priti®multidisc ZrO₂ white Extra Translucent</p>	 <p>priti®multidisc ZrO₂ white High Translucent</p>

Translucency

priti® multidisc ZrO₂

Suitable for all conventional open milling machines with adapter for **blank diameter 98.5 mm**. In addition the **blank diameter 95 mm** is available in Extra Translucent with a height of **18 mm**.



priti® multidisc ZrO₂ – Opaque with a **translucency of 35 %**, Sintering temperature 1,450° C
Flexural strength > **1,150 MPa** - Released for bridges up to 16 units

OPAQUE	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
monochrome in VITA® shades	A1, A2, A3, A3,5, A4, B2, C2, D2	14, 20

priti® multidisc ZrO₂ – Extra Translucent with a **translucency of 45 %**, Sintering temperature 1,450° C
Flexural strength > **1,150 MPa** - Very High Aesthetics, Released for bridges up to 16 units

EXTRA TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
multicolor	A light (shade range: A1-A3), A dark (shade range: A3,5-A4), B light (shade range: B1-B2), B dark (shade range: B3-B4), C light (shade range: C1-C2), C dark (shade range: C3-C4), D light (shade range: D2-D4), priti® bleach (shade range: 0M1, 0M2, 0M3, 1M1)	14, 18, 20, 25

Blank diameter 95 mm in Extra Translucent with a height of **18 mm** available.

priti® multidisc ZrO₂ – Multi Translucent with a **translucency gradient of >49 % to ~40%**, Sintering temperature 1,450° C
Flexural strength from > **800 MPa to 1,150 MPa**; typical value > 1,100 MPa - Released for single crowns and bridges up to 16 units - Highest Aesthetics

MULTI TRANSLUCENT	SHADES	HEIGHTS IN MM
gradual transition in VITA® shades	A1, A2, A3, A3,5, A4, B1, B2, B3, B4, C1, C2, C3, C4, D2, D3, D4, 0M1, 0M2, 0M3	16, 20 and 25 mm

priti® multidisc ZrO₂ – Translucent with a **translucency of 40 %**, Sintering temperature 1,450° C
Flexural strength > **1,150 MPa** - High Aesthetics - Released for bridges up to 16 units

TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	14, 20, 25
monochrome in VITA® shades	A1, A2, A3, A3,5, A4, B2, C2, D2	14, 20, 25

priti® multidisc ZrO₂ – High Translucent with a **translucency of 49 %**, Sintering temperature 1,450° C
Flexural strength > **650 MPa** - Highest Aesthetics - Released for bridges up to 3 units

HIGH TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
multicolor	A light (shade range: A1-A3), A dark (shade range: A3,5-A4), B light (shade range: B1-B2), B dark (shade range: B3-B4), C light (shade range: C1-C2), C dark (shade range: C3-C4), D light (shade range: D2-D4), priti® bleach (shade range: 0M1, 0M2, 0M3, 1M1)	14, 18, 20, 25